


PART NO.	
U-G-04WS-W-03	U-G-04WS-W-04
Housing&Black	Housing&White

SPECIFICATIONS


- 1.Rating : DC 30V 1.5A
- 2.Contact Resistance: ≤50mΩ
- 3.Insulation Resistance:
≥1000mΩ Min DC250V
- 4.Operating Temperature Range:
-40°C+85°C



③	Shell	—	1	SPCC	—	—
②	Contact	—	4	BRASS	—	—
①	Housing	—	1	PBT	Black/White	—
ITEM	PART NAME	TER/NO.	QTY.	MATERIAL	FINISHING	REMARK

DRAWN		DATE	
QFENG.XU	2014/6/17		
CHECKED		TITLE:	
		USB CONNECTOR	
APPROVALS		DRAWING NO.	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	30~Ø以上 10~30 5~10 ~3	±0.30 ±0.25 ±0.20 ±0.15	ANGLE	±2°	UNIT: mm	SCALE: 1:1	PROJ.	SHEET 1 OF 1
	A		NEW												



HONGSHAN ELECTRONICS CO., LTD