



SWITCH CONNECTOR

SCHEMATIC	
Model	DC-025LBM-5A
Center Pin	Ø2.0 mm
	Ø2.5 mm

	MATERIAL	PLATING
center pin	brass	tin
terminal 1	brass	tin
terminal 2	copper alloy	tin
terminal 3	brass	tin
plastic	PA66	

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°	DSND	DATE	SCALE: N/A	MODEL TYPE: DC POWER JACK		
△X					$L \leq 4$	±0.2	DWN	DATE	VIEW:	PART NO.:		
△X					$4 < L \leq 16$	±0.3	CHKD	DATE	UNIT: mm	DWG NO.:		
△X					$16 < L \leq 63$	±0.4	APPD	DATE	SIZE: A4	DC-026LBM-5A-2.0		
					$L > 63$	±0.5				WEIGHT	SHEET	REVISION
					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO., LIMITED			1.0g	1/1	A0