


PCB Layout

SPECIFICATIONS
 1.Rating : DC 30V 1.0A
 2.Contact Resistance: ≤50mΩ
 3.Insulation Resistance:
 ≥1000mΩ Min DC250V
 4.Operating Temperature Range:
 -40 °C+85 °C

PART NO.	
U-G-04DD-W-01	U-G-04DD-W-02
Housing & Black	Housing & White



③	Shell	—	1	SPCC	Ni Plated	—
②	Contact	—	4	Copper Alloy	Ag Plated	—
①	Housing	—	1	Nylon	White/Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE				

DRAWN JKUN.LU 2014/9/29
 TITLE: USB CONNECTOR
 ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE		30~Ø以上	±0.30	ANGLE	±2°	DRAWING NO.
		10~30	±0.25			
		5~10	±0.20			
		~5	±0.15			
APPROVALS		PART NO.	U-G-04DD-W-01	PROJ:	SHEET 1 OF 1	