



XKLB

SWITCH CONNECTOR

SCHEMATIC	
Model	DC-012-2.5A
Center Pin	Ø2.0 mm
Center Pin	Ø2.5 mm

	MATERIAL	PLATING
center pin	copper	nickel
terminal 1	brass	tin
terminal 2	copper alloy	tin
terminal 3	brass	tin
plastic	PBT	

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE:	
						DWN	DATE	VIEW:	DC POWER JACK	
△ X					ANGULAR ±5° L ≤ 4 ±0.2	CHKD	DATE	UNIT: mm	PART NO.:	
△ X					4 < L ≤ 16 ±0.3	APPD	DATE	SIZE: A4	DWG NO.:	
△ X					16 < L ≤ 63 ±0.4				DC-012-2.5A-2.5	
MARK					L > 63 ±0.5	XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	
REVISIONS										SHEET
										REVISION
										1.0g
										1/1
										A0