


Recommended PCB Layout Top View

Model N o.	PJ-242 A-SMT	PJ-242 B-SMT	PJ-242 C-SMT	PJ-242D -SMT
Schematic				
PIN				
1	sleeve	sleeve	sleeve	sleeve
2	tip	tip	tip	tip
3	ring 1	ring 1	ring 1	ring 1
4	ring 2	ring 2	ring 2	ring 2
10	NP	tip switch	NP	tip switch
11	NP	NP	ring 1 switch	ring 1 switch



	MATERIAL	PLATING
terminal 1	copper alloy	gold flash
terminal 2	Ti-Cu	gold flash
terminal 3	copper alloy	gold flash
terminal 4	copper alloy	gold flash
terminal 10	brass	gold flash
terminal 11	brass	gold flash
plastic	PA10T	

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE:
△ X					ANGLAR ±5°	DWN	DATE	VIEW:	PART NO.:
△ X					L ≤ 4 ±0.2	CHKD	DATE	UNIT: mm	DWG NO.:
△ X					4 < L ≤ 16 ±0.3	APPD	DATE	SIZE: A4	PJ-242X-SMT
					16 < L ≤ 63 ±0.4	KXB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT
					L > 63 ±0.5				1.0g
									SHEET
									1/1
									REVISION
									A0