

Recommended P.C.B Layout

MATERIAL



Insulator : NY66+30% Glass fiber
Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
Insulation Resistance : 5000MΩMin. at DC 500V
Contact Resistance : 20mΩMax. at DC 100mA
Dielectric Voltage : AC 500V for one minute
Operation Temperature : -40°C to + 105°C

210-8 1- 05 G B 01
1 2 3 4 5 6

1. 8: Green Product
2. 1: Single row
2: Dual rows
3. No. of contacts per row
4. G: Gold flash
S: Selective
T: Tin plated
5. B: Black Insulator
R: Red Insulator
W: Nature color Insulator
U: Blue Insulator
6. Pinrex internal code.

				TOLERANCE		 OLD PART NO.		TITLE		 频锐科技股份有限公司 PINREX TECHNOLOGY CORP.
C	修正规格尺寸	2016/12/16	.0 = ±.30	UNITS : mm	DRAWER	廖小芳	CHECK	PIN HEADER 2.54*2.54mm STRAIGHT TYPE, SINGLE ROW		
B	REVISE SIZE	2008/03/07	.00 = ±.20	SCALE	SIZE	SHEET	REV.	APP'D	NEW PART NO.	DRAW NO.
A	RELEASE	2006/07/10	.0000 = ±.XXX	NONE	A4	1 OF 1	C		210-81-05GB01	210-81-05GB01(C版)
REV.	DESCRIPTION	DATE	ANG.=±3'							