

Recommended P.C.B Layout

MATERIAL

Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP

Insulation Resistance : 5000MΩMin. at DC 500V



Contact Resistance : 20mΩMax. at DC 100mA

Dielectric Voltage : AC 500V for one minute

Operation Temperature : -40°C to + 105°C

210-9 1- 04 G B 02  
 1 2 3 4 5 6

1. 5: Normal parts (30% Glass fiber PBT)
- 7: Green Product (30% Glass fiber PBT)
- 9: Green Product High Temp (NYLON 9T)
2. 1: Single row
- 2: Dual rows
3. No. of contacts per row
4. G: Gold flash
- S: Selective
- T: Tin plated
5. B: Black Insulator
6. Pinrex internal code.

			TOLERANCE	 UNITS : mm	OLD PART NO.		TITLE PIN HEADER 2.54*2.54mm STRAIGHT TYPE, SINGLE ROW	 频锐科技股份有限公司 PINREX TECHNOLOGY CORP.
C	REVISE DIMENSIONS	2016/06/20	.0 =±.30		DRAWER 廖小芳	CHECK		
B	REVISE DIMENSIONS	2007/09/01	.00 =±.20					
A	RELEASE	2005/08/29	.0000=±.000					
REV.	DESCRIPTION	DATE	ANG.=±3'	SCALE NONE	SIZE A4	SHEET 1 OF 1	REV. C	APP'D
							NEW PART NO. 210-91-04GB02	DRAW NO. 210-91-04GB02(C版)