



Recommended P.C.B Layout

MATERIAL

Insulator : NY66+30% Glass fiber
 Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
 Insulation Resistance : 5000MΩMin. at DC 500V
 Contact Resistance : 20mΩMax. at DC 100mA
 Dielectric Voltage : AC 500V for one minute
 Operation Temperature : -40°C to + 105°C

210-8 2- 03 G B 01
 1 2 3 4 5 6

- 1. 8: Green Product
- 2. 1: Single row
- 2: Dual rows
- 3. No. of contacts per row
- 4. G: Gold flash
- S: Selective
- T: Tin plated
- H: 15u" Gold plated
- 5. B: Black Insulator
- K: Dark Green Insulator
- Y: Yellow Insulator(123C)
- 6. Pinrex internal code.

				TOLERANCE				OLD PART NO. PH1S-203GB 116/61/30		TITLE PIN HEADER 2.54*2.54mm STRAIGHT TYPE, DUAL ROWS		頻銳科技股份有限公司 PINREX TECHNOLOGY CORP.
				.0 =±.35 .00 =±.25 .000 =±.XXX .0000=±. ANG.=±3'		UNITS : mm		DRAWER <i>LiuHui</i>		CHECK		
A	RELEASE	2008/04/15		SCALE	SIZE	SHEET	REV.	APP'D	NEW PART NO.	DRAW NO.		
REV.	DESCRIPTION	DATE		NONE	A4	1 OF 1	A		210-82-03GB01	210-82-03GB01		