



Recommended P.C.B Layout

MATERIAL

Insulator : NYLON 66 + 30% Glass fiber
Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
Insulation Resistance : 5000MΩMin. at DC 500V
Contact Resistance : 20mΩMax. at DC 100mA
Dielectric Voltage : AC 500V for one minute
Operation Temperature : -40°C to + 105°C

210-8 2- 05 G B 04
1 2 3 4 5 6

- 1. 8: Green Product
- 2. 1: Single row
- 2: Dual rows
- 3. No. of contacts per row
- 4. G: Gold flash
- S: Selective
- T: Tin plated
- 5. B: Black Insulator
- 6. Pinrex internal code.

				TOLERANCE				OLD PART NO.		TITLE	
				.0 = ±.30		UNITS : mm		DRAWER		CHECK	
				.00 = ±.20				Chunyan		PIN HEADER 2.54*2.54mm	
				.000 = ±.XXX				SHEET		STRAIGHT TYPE, DUAL ROWS	
B		REVISE SIZE		2008/03/03		SCALE		REV.		NEW PART NO.	
A		RELEASE		2006/01/03		NONE		1 OF 1		210-82-05GB04	
REV.		DESCRIPTION		DATE		SIZE		APP'D		DRAW NO.	
						A4		B		210-82-05GB04(B版)	

