



Recommended P.C.B Layout

MATERIAL

Contact Pin : Brass  
 Insulation : NY6T

SPECIFICATION

Current Rate : 3 AMP  
 Insulation Resistance : 5000MΩMin. at DC 500V  
 Contact Resistance : 20mΩMax. at DC 100mA  
 Dielectric Voltage : AC 500V for one minute  
 Operation Temperature : -40°C to + 105°C

210-9 2- 05 G B 02  
 1 2 3 4 5 6

- 1. 7: Green Product
- 9: Green Product High Temp
- 2. 1: Single row
- 2: Dual rows
- 3. No. of contacts per row
- 4. G: Gold flash
- S: Selective
- T: Tin plated
- 5. B: Black Insulator
- 6. Pinrex internal code.



				TOLERANCE		 UNITS : mm		OLD PART NO.		TITLE	
D	修改材質	2018/05/21	.0 =±.30	 SCALE NONE SIZE A4		DRAWER 袁丽娜		CHECK 李劍		PIN HEADER 2.54*2.54mm STRAIGHT TYPE, DUAL ROWS	
C	REVISE HOUSING SIZE	2011/08/02	.00 =±.20	SHEET 1 OF 1		REV. A		APP'D 李劍		 PINREX TECHNOLOGY CORP.	
B	REVISE SIZE	2008/08/27	.000 =±.XXX	NEW PART NO. 210-92-05GB02						DRAW NO. 210-92-05GB02(D版)	
A	RELEASE	2006/12/20	.0000=±.								
REV.	DESCRIPTION	DATE	ANG.=±3'								