

Recommended P.C.B Layout


**MATERIAL**  
 Insulator: NY6T UL94-V0  
 Contact Pin : Brass

**SPECIFICATION**

Current Rate : 3 AMP  
 Insulation Resistance : 5000MΩMin. at DC 500V  
 Contact Resistance : 20mΩMax. at DC 100mA  
 Dielectric Voltage : AC 500V for one minute  
 Operation Temperature : -40°C to + 105°C

210-9 2- 03 G B 01  
 1 2 3 4 5 6

1. 7: Green Product
- 9: Green Product High Temp
2. 1: Single row
- 2: Dual rows
3. No. of contacts per row
4. G: Gold flash
- S: Selective
- T: Tin plated
5. B: Black Insulator
- W: White Insulator
6. Pinrex internal code.



				TOLERANCE		UNITS : mm		OLD PART NO.		TITLE		 频锐科技股份有限公司 PINREX TECHNOLOGY CORP.
D	增加材質與防火等級	2018/06/11	.0	=±.30	SCALE	SIZE	SHEET	REV.	CHECK	NEW PART NO.	DRAW NO.	
C	REVISE HOUSING SIZE	2011/07/21	.00	=±.20	NONE	A4	1 OF 1	D	李劍	210-92-03GB01	210-92-03GB01(D版)	
B	REVISE DIMENSIONS	2007/09/27	.000	=±.XXX					APP'D			
A	RELEASE	2005/04/25	.0000=±.	ANG.=±3'					李劍			
REV.	DESCRIPTION	DATE										