

PJ-3135-

SPECIFICATION

- 1 Rating : DC 30V 10A
- 2 Contact resistance : $\leq 20m\Omega$
- 3 Insulation resistance : $\geq 100M\Omega$
- 4 Withstand voltage : 500VAC
- 5 Insertion and extraction force : 3-20N
- 6 Life test : 5,000 cycles

SCHMATIC

PJ-3135-	PJ-3136-

SWITCH CONNECTOR

Ø3.5 MATING PLUG

R:red	G:green
Y:yellow	B:black
W:white	T:transparent

	MATERIAL	
terminal 1	copper alloy	5
terminal 2	copper alloy	5
terminal 3	copper alloy	5
terminal 4	copper alloy	5
plastic	PA9T	

DSND	DATE	SCALE: NA	MC
DWN	DATE	VIEW:	PA
CHKD	DATE	UNIT: mm	DW
APPD	DATE	SIZE: A4	W

MARK	DESCRIPTION	REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
△x						ANGULAR ±5°
△x						L ≤ 4 ±0.2
△x						4 < L ≤ 16 ±0.3
						16 < L ≤ 63 ±0.4
						L > 63 ±0.5

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

XKB INDUSTRIAL PRECISION CO., LIMITED