



RECOMMENDED P.C.B LAYOUT

MATERIAL

Insulator:PA6T UL94V-0

Contact pin: Brass

Contact plated:Gold /Tin Over Nickel

Specification

Current Rating : 3Amp

Insulation Resistance : 1000MΩ Min

Contact Resistance:20 Milliohms Max

Dielectric withstanding Voltage:AC 500V

Operation Temperature : -40 °C -- +105 °C

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD
CHECKED:	DATE:	
DRAMN:	DATE:	TITLE: 210S-2*20P 三层塑胶 L=16.7mm
LXF	2009-06-05	Part No. B-2100S40P-E000 UNIT mm SCALE Free FILE NO. S007200067
		REV. A