



Specification
Insulator Material: Polyeser, UL94V-0
Standard: PA6T
Contact Material: Brass
Current Rating : 1.5Amp
Contact Resistance: 20 Milliohms Max
Insulation Resistance : 1000M Ω Min.
Dielectric withstanding Voltage: AC 500V
Operation Temperature : -40 $^{\circ}$ C -- +105 $^{\circ}$ C

APPROVED:	DATE:	CLIENT P/N /			
CHECKED:	DATE:	UNIT mm			
DRAWN:	DATE:	SCALE free		\varnothing	∇
LXF	2008-09-27	FILE NO.	Chantw-210-20002	REV.	A
TOLERANCE TABLE					
.0	± 0.20				
.00	± 0.10				
.000	± 0.05				

深圳市灿科盟实业有限公司
Chantw CHANKEMENG INDUSTRY CO., LTD

TITLE:
 210-2S-1*XP L=8.8mm