



PCB Layout

SPECIFICATION
 Current Rate:3Amp
 Contact Resistance:20mΩ MAX.at DC 1A
 Insulation Resistance:1000MΩ MIN.atDC500V
 Dielectric Strength:AC500V PER minute
 Operation Temperature:-40°to +105°

MATERIAL
 Insulator:Polyester ,UL94V-0
 Standard:PA6T
 CONTACT:Brass
 Contact plated: Gold Over Nickel
 Poles:2~40P (Double)
 Color:Black

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	TITLE:			
CHECKED:	DATE:	220S-2*XP H=8.5MM (PA6T)			
DRAWN:	DATE:	CLIENT P/N	UNIT	SCALE	REV.
LXF	2008-04-29	/	mm	free	A
		FILE NO.	Clkmtw-220-00016		

深圳市灿科盟实业有限公司
 CkmtwCHANKEMENG INDUSTRYCO., LTD