

RECOMMENDED P.C.B LAYOUT

Specification

Insulator Material: Polysulf; UL94V-0

Standard:P.B.T

Contact plated: Gold Over Nickel

Poles:2~40P


Current Rating : 3Amp

Contact Resistance:20 Milliohms Max

Insulation Resistance : 1000MΩ Min.

Dielectric withstanding Voltage:AC 500V

Operation Temperature : -40 °C -- +105 °C

核准:	日期:	 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD
业务:	日期:	
制图:	日期:	品名规格: 210R-1*13P L=13.8MM
L.YF	2009-12-28	客户料号: B-2100R13P-A010
未注公差表		单位: mm
X.X ±0.2		比例: /
X.XX ±0.10		图纸编号: Chantw-210-00007
X.XXX ±0.050		版本: A