



SPECIFICATIONS

Material:

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Contacts: Brass

Contact plating: Au or Sn over Ni

Plating: Gold Flash

Electrical Characteristics:

Contact Resistance: 20mΩ Max.

Insulator Resistance: 1000MΩ Max.

Withstanding Voltage: AC/1000V

Current Rating: 3 AMP

Operation Temperature: -40°C ~ +105°C

| Poles | Part No. | Dimension mm | | |
|-------|------------|--------------|-------|-------|
| | | A | B | C |
| 6 | 300SMT-6P | 14.82 | 12.82 | 5.08 |
| 8 | 300SMT-8P | 17.98 | 16.18 | 7.62 |
| 10 | 300SMT-10P | 19.90 | 17.70 | 10.16 |
| 12 | 300SMT-12P | 22.44 | 20.24 | 12.70 |
| 14 | 300SMT-14P | 24.98 | 22.78 | 15.24 |
| 16 | 300SMT-16P | 27.52 | 25.32 | 17.78 |
| 18 | 300SMT-18P | 30.06 | 27.86 | 20.32 |
| 20 | 300SMT-20P | 32.60 | 30.40 | 22.86 |
| 24 | 300SMT-24P | 37.68 | 35.48 | 27.94 |
| 26 | 300SMT-26P | 40.22 | 38.02 | 30.48 |
| 30 | 300SMT-30P | 45.30 | 43.10 | 35.56 |
| 34 | 300SMT-34P | 50.38 | 48.18 | 40.64 |
| 40 | 300SMT-40P | 58.00 | 55.80 | 48.26 |
| 44 | 300SMT-44P | 63.08 | 60.88 | 53.34 |
| 50 | 300SMT-50P | 70.70 | 68.50 | 60.96 |

TOLERANCE TABLE

| | |
|------|-------|
| .0 | ±0.20 |
| .00 | ±0.10 |
| .000 | ±0.05 |

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

SXA

2019-05-14

TITLE:

300SMT-XP (2.54贴面筒牛)


深圳市矽科盟实业有限公司
 CHANKLEMENT INDUSTRY CO., LTD

Part No. B-3000NXXP-0110

| UNIT | mm | SCALE | Free | REV. | A | WY02 |
|----------|-----------------|-------|------|------|---|------|
| FILE NO. | Chartw-300-0023 | | | | | |