



**SPECIFICATION:**  
**Current Rating:**3.0AMP  
**Contact Resistance:**20m Ω (max)  
**Insulation Resistance:**1000M Ω Min at 500V DC  
**Dielectric Strength:**500V AC Per 1 Minute  
**Operating Temperature:**-40 °C TO +105 °C

**MATERIALS:**  
**Insulator:** PA6T (UL 94V-0)  
**Contact:**Brass  
**Contact plated:** Gold Over Nickel

Poles	Part No.	Dimension mm		
		A	B	C
10	310S-10P	31.90	10.16	18.60
12	310S-12P	34.44	12.70	21.14
14	310S-14P	36.98	15.24	23.68
16	310S-16P	39.52	17.78	26.22
20	310S-20P	44.60	22.86	31.30
24	310S-24P	49.68	27.94	36.38
26	310S-26P	52.22	30.48	38.92
30	310S-30P	57.30	35.56	44.00
34	310S-34P	62.38	40.64	49.08
40	310S-40P	70.10	48.26	56.70
50	310S-50P	82.70	60.96	69.40
60	310S-60P	95.40	73.66	82.10
64	310S-64P	100.48	78.74	87.18

**TOLERANCE TABLE**

.0	±0.30
.00	±0.20
.000	±0.05

<b>APPROVED:</b>	<b>DATE:</b>	<b>TITLE:</b> 310R-60P (PA6T)
<b>CHECKED:</b>	<b>DATE:</b>	
<b>DRAWN:</b> LYF	<b>DATE:</b> 2008-04-07	Part No. B-3100R60P-A110 UNIT mm SCALE Free FILE NO. Ckmtw-310-00016 REV. A


**深圳市灿科盟实业有限公司**  
 CHANKEMENG INDUSTRYCO., LTD