

**SPECIFICATIONS**

Rated(额定参数): 150V,10A  
 Dielectric strength(抗电强度): AC1500V/1 Minute  
 Insulation Resistance(绝缘电阻):1000MΩ Min  
 Contact Resistance(接触电阻):20mΩ Max  
 Screw Torque(扭矩): 0.2Nm (1.7Lb.in)  
 Wire Range(线径):26~16AWG  
 Strip length(剥线长度):5~6mm  
 Temp. range(操作温度): -40°C~+105°C  
 MAX Soldering(瞬时温度):+250°C,5s

Housing Material(塑件): PA66 (UL94 V-0)  
 Contact(端子): Brass, Tin plating(黄铜镀锡)  
 Wire protector(弹片): Brass(黄铜), Ni plating(镀镍)  
 Screw (螺丝): M2.0, Steel, Zinc plating(钢,镀锌)

PITCH RANGE		NOMINAL DIMENSION RANGE	
IN	MM	IN	MM
OVER	6	OVER	30
TO	10	TO	60
OVER	10	TO	100
TO	24	TO	150
±0.10	±0.15	±0.25	±0.30
		±0.30	±0.50
		±0.50	±0.70
		±1.00	

**Ordering Information**




**JL 124D - XXX XX X X 1**

Pitch  
 350=3.50PH  
 381=3.81PH  
 396=3.96PH

No.of pins  
 2P,3P,4P~24P

Housing Color  
 B=Black  
 G=Green  
 U=Blue  
 R=Red  
 W=White  
 Y=Yellow  
 O=Orange  
 E=Grey

Packing  
 O=Pe bag  
 T=Tube  
 A=Troy



Recommended P.C.B Layout(Top Side)

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	BEN	17.01.03	SCALE	FIT	PART NO.	TITLE:
				XX	±				UNIT	mm		
A0	2017.01.03	NEW DRAWING		X:XX	±	CHECK					JL 124D-XXXXXXXX1	3.50/3.81/3.96mm Terminal Blocks
1				Angle	±3'	APPROVE						Femle 180°

**JIN** 深圳市锦凌电子有限公司  
 SHENZHEN JINLING ELECTRONIC CO.,LTD  
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992