



MECHANICAL

Insulator material:
 PBT@glass-fibre reinforced
 UL 94v-0
 plastic:Brass

Nut specifications:

Shell:nicdel(or tin,gold)plated
 Number of cntact:04.
 Durabil tty:5000 cycles

ELECTRICAL

Current rating:5Amp

Dielectric withstanding voltage:AC

500vmin (500v dc)

500m max

Contactresistance:

25m max

Working temperayure:-50° c--+

150° c

APPROVED:	DATE:	深圳市灿科盟实业有限公司 GkmtwCHANKLEMENT INDUSTRYCO., LTD
CHECKED:	DATE:	

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

DRAWN:	DATE:	TITLE: USB-A-M-4P 焊线 折叠式 铁壳 白胶 端子镀金					
SXA	2019-05-13						
CLIENT P/N	U-USBW04P-M005	UNIT	mm	SCALE	free	REV.	HLW0
FILE NO.							