

SPECIFICATIONS

Rated (额定参数): 300V, 1.5A
 Dielectric strength (抗电强度): AC1500V/1 Minute
 Insulation Resistance (绝缘电阻): 1000MΩ Min
 Contact Resistance (接触电阻): 20mΩ Max
 Screw Torque (扭矩): 0.40Nm (3.5lb.in)
 Wire Range (线径): 12~24AWG
 Strip length (剥线长度): 4.5~5mm
 Temp. range (操作温度): -40°C~+105°C
 MAX Soldering (瞬时温度): +250°C, 5s




Housing Material (塑件): PA66 (UL94 V-0)
 Contact (端子): Brass, Tin plating (黄铜镀锡)
 Wire protector (弹片): Bronze (磷铜), Ni plating (镀镍)
 Screw (螺丝): M2.5, Steel, Zinc plating (钢 镀锌)

PITCH RANGE	NOMINAL DIMENSION RANGE					
	IN MM		IN MM		IN MM	
OVER 6	OVER 10	OVER 30	OVER 60	OVER 100	OVER 150	OVER 150
TO 6	TO 10	TO 30	TO 60	TO 100	TO 150	TO 150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70
						±1.00

Ordering Information

JL 301 - 500 XX X X 1

Pitch 500=5.0PH
 No. of pins 2P, 3P, 4P~24P
 Housing Color
 B=Black
 G=Green
 U=Blue
 R=Red
 W=White
 Y=Yellow
 O=Orange
 F=Grey
 Packing
 0=Pe bag
 T=Tube
 A=Tray



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE	BEN	17.01.04	SCALE	FIT	TITLE:
A0	2017.01.04	NEW DRAWING		CHECK			A4	1/1	JL301-500XXXX1
1									5.00mm Terminal Blocks Female 180°

JILIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992