






Cixi Dibo Electronics Co.,LTD

产品规格书
product specification



电 气 性 能 /Electrical
参考标准/Standard: UL IEC
额定电压/Rated voltage: 300V 250V
额定电流/Rated current: 8A 15A
接触电阻/Contact resistance: 20mΩ
使用线径/Wire range: 26-14AWG 1.5mm²
耐电压/Withstanding voltage: AC2000V/1Min
绝缘电阻/Insulation resistance: 500MΩ/DC500V

机 械 性 能 /Mechanical
温度范围/Temp.Range: -40° C~+105° C
扭 矩/Torque: 0.4Nm(3.5lb`in)
剥线长度/Strip length: 6-7mm

尺 寸 /Dimensions
间距/Pitch: 5.0mm
极数/Poles: 2P-24P

材 质 及 电 镀 /Material
塑 件 /Housing: PA66, UL94V-0
螺 丝 /Screws: M2.5, steel Zinc plated
方 针 /Pin header: Brass, Ni plated
弹 片 /Snapnet: Phosphor bronze, Ni plated

TOLERANCES EXCEPT AS NOTED

linear dimension(Tolerances Standard GB/T 14486-2009)											
linear dimension											
tolerance	±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25
variable range	to 6	over 6 to 10	over 10 to 18	over 18 to 30	over 30 to 50	over 50 to 80	over 80 to 120	over 120 to 160	over 160 to 200	over 200 to 250	all to 5
tolerance	±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25

订购方式：
HOW TO ORDER

型号/Model

-

极数/POLE

-

封装/Package

-

颜色/Color

-

客户需求/Custom Request

尺寸/Size

-

比例/Scale

-

颜色/Color

-

客户需求/Custom Request

单位/Units

-

比例/Scale

-

颜色/Color

-

客户需求/Custom Request

单位/Units

mm

尺寸/Size

A4

比例/Scale

比例

第一视角/THIRD ANGLE PROJECTION

Cixi Dibo Electronics Co.,LTD

名称/NAME

DB126V-5.0