

SPECIFICATIONS

Rated(额定参数): 300V,8A
 Dielectric strength(抗电强度): AC1500V/1 Minute
 Insulation Resistance(绝缘电阻):1000MΩ Min
 Contact Resistance(接触电阻):20mΩ Max
 Temp. range(操作温度): -40℃~+105℃
 MAX Soldering(瞬时温度):+250℃,5s

Housing Material(塑件): PA66 (UL94 V-0)
 Contact(端子): Brass, Tin plating(黄铜镀锡)

PITCH RANGE	NOMINAL DIMENSION RANGE										
	IN MM		IN MM		IN MM						
TO 6	OVER 6	TO 10	OVER 10	TO 30	OVER 30	TO 60	OVER 60	TO 100	OVER 100	TO 150	OVER 150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.30	±0.50	±0.70	±1.00			

Ordering Information



JL15EDGRC-XXX XX G X 1

Pitch
 350=3.5PH
 381=3.81PH

No. of pins
 2P~24P

Housing Color
 B=Black
 G=Green
 U=Blue
 R=Red
 W=White
 Y=Yellow
 O=Orange
 E=Grey

Packing
 0=Pe bog
 T=Tube
 A=Troy



OPERATION		DRAW		BEN		17.12.22		SCALE		FIT		PART NO.		JL15EDGRC-XXXXXXGX1	
X.X		±0.30						UNIT		mm		SHENZHEN JINLING ELECTRONIC CO.,LTD		3.50/3.81mm Pitch Male Pluggable Terminal Blocks	
X.XX		±0.20		CHECK				SIZE		A4		Tel: 86-755-2997-5806/5802		Fax: 86-755-2997-5992	
X.XXX		±0.10						SHEET		1/1		Title:			
Angle		±3°		APPROVE				PROJ.							
DIM		TOL													
CHANGE		4													
MODIFICATION DESCRIPTION		3													
DATE		2													
REV		1													
NEW DRAWING		A													
2017.12.22		A													

JINLING 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992