

Recommended P.C.B Layout

MATERIAL



Insulator : NY66 + 30% Glass fiber  
Contact Pin : Brass

SPECIFICATION

Current Rate : 2.5 AMP  
Dielectric voltage : 250V AC for one minute  
Insulation Resistance : 1000MΩMin.  
Contact Resistance : 20mΩMax

744-8 1-03 T W 10  
1 2 3 4 5

1. 8: Green Product
2. No. of contacts per row
3. G: Gold flash  
S: Selective  
T: Tin plated
4. W: Nature Color Insulator
5. Pinrex internal code.

E	标示PIN1位置	2013/01/10	TOLERANCE	 UNITS : mm	OLD PART NO.		TITLE		 頻銳科技股份有限公司 PINREX TECHNOLOGY CORP.
D	ADD TOLERANCE	2011/06/01	.0 =±.50		DRAWER 尹小姜	CHECK	2.54mm WIRE TO BOARD HEADER DIP 180° TYPE		
C	REVISE ILLUSTRATION	2008/10/24	.00 =±.30	SCALE NONE	SIZE A4	SHEET 1 OF 1	REV. E	APP'D	NEW PART NO. 744-81-03TW10
B	ADD DIMENSIONS	2006/05/09	.000 =±.XXX						
A	RELEASE	2005/09/19	.0000=±.						
REV.	DESCRIPTION	DATE	ANG.=±3'					DRAW NO. 744-81-03TW10(E版)	