



Recommended P.C.B Layout

MATERIAL

Insulator : NY66+30% Glass fiber
Contact Pin : Brass

SPECIFICATION

Current Rate : 4 AMP
Dielectric voltage : 250V AC for one minute
Insulation Resistance : 1000MΩMin.
Contact Resistance : 20mΩMax

744-8 1-04 T B 1B
1 2 3 4 5

1. 8: Green Product
2. No. of contacts per row
3. G: Gold flash
S: Selective
T: Tin plated
4. B: Black Insulator
5. Pinrex internal code.



				TOLERANCE		OLD PART NO.		TITLE	
				.0 =±.50		DRAWER 杨海琴		2.54mm WIRE TO BOARD HEADER	
				.00 =±.30		CHECK 李剑		DIP 180° TYPE	
				.000 =±.XXX		SCALE NONE		PINREX 頻銳科技股份有限公司	
A RELEASE		2018/05/28		.0000=±.		SIZE A4		PINREX TECHNOLOGY CORP.	
REV. DESCRIPTION		DATE		ANG.=±3'		SHEET 1 OF 1		NEW PART NO.	
						REV. A		744-81-04TB1B	
						APP'D 李剑		DRAW NO.	
								744-81-04TB1B	