



Recommended P.C.B Layout

MATERIAL  
 WAFER:NY6T UL 94V-0  
 CONTACTS:BRASS  
 PLATING:IN OVER NICKEL  
 SPECIFICATION



CURRENT RATE:

Wire size	#20	#22	#24	#26	#28	#30
Ampere	5A	5A	4A	3A	2A	1A

Voltage Rating:50V AC,DC  
 OPERATING TEMPERATURE:-25°C~+85°C  
 Contact Resistance:20mΩ Max  
 Insulation Resistance:100MΩ Min  
 Withstanding Voltage:500V AC/minute

733-7 2- 08 T B 1 0  
 1 2 3 4 5 6 7

1. 7: Green Product  
9: Green Product High Temp
2. 2: Right angle type
3. No. of contacts
4. T: Tin plated  
H: 15u" Gold plated
5. B: Black Insulator
6. 1: With post
7. Pinrex internal code.



F	增加AMP 總表	2019/01/18
E	無縫改有縫	2017/12/01
D	修正材質	2015/11/14
C	增加尺寸:8.00	2014/03/11
B	REVISE DESCRIPTION	2013/05/11
REV.	DESCRIPTION	DATE

TOLERANCE	
.0	=±.30
.00	=±.25
.000	=±.XXX
.0000=±.	
ANG.	=±3'

UNITS : mm	
SCALE	NONE
SIZE	A4

OLD PART NO.		DRAWER 袁麗娜		CHECK 李劍	
SHEET	1 OF 1	REV.	<b>F</b>	APP'D	李劍

TITLE	POWER CONNECTOR MO 3.0mm HEADER RIGHT ANGLE TYPE
NEW PART NO.	733-72-08TB10

頻銳科技股份有限公司 PINREX TECHNOLOGY CORP.	DRAW NO.	733-72-08TB10(F版)
---------------------------------------	----------	-------------------