




RoHS Compliant



技术要求:

1. 芯线导体不能断或缺少
2. 阻抗: 50 欧姆
3. 不可有短路, 同轴线表面不能有刮伤
4. 端子为MHF IPEX端子, 确保产品品质, 产品拉拔力要达到1.2KGf.

4	Connector	1	MHF Au Plating
3	PCB	1	48.0mm/7.5/0.6mm
2	Paster	1	47.0*6.5*T0.1mm
1	Coaxial Cable	1	O.D. 1.13mm (BLACK)
NO	PART NAME	Q'TY	DESCRIPTION

				TOLERANCE		 <b>华创翔科技</b> HUACHUANGXIANGTECHNOLOGY		TITLE: Wifi Antenna L=150mm MHF CABLE			
				LINEAR	ANGLES			PART NO. 20150310001			
				X±0.40	X'±	APPD: Jason	MAT'L:	DWG NO. HCX001-02			
				.X±0.30	.X'±	CHKD: Schumi	FINISH:	 UNITS: MM SCALE: 1:1	SHEET: 1 OF 1	REV: A	
A		Kevin	2015/03/10	.XX±0.20	.XX'±	DRWN: Terry	Q'TY:				
REV	ECN NO.		DATE	.XXX±0.10	.XXX'±						