






MRK.	DATE	REVISION	SIGN
△			



P.C.B DIMENSION



Specification

- Rating : 25mA, 12V DC (Switching)
25mA, 24V DC (None-Switching)
- Contact Resistance : 100mΩ Max
- Insulation Resistance : 100MΩ Min
- Operating Force : 700gf Max
- Life cycle : 10,000 steps

		Real Code				
		C	1	2	4	8
16 P o s i t i o n	0	●				
	1	●	●			
	2	●		●		
	3	●	●	●		
	4	●			●	
	5	●	●		●	
	6	●		●	●	
	7	●	●	●	●	
	8	●				●
	9	●	●			●
A	●		●		●	
B	●	●	●		●	
C	●			●	●	
D	●	●		●	●	
E	●		●	●	●	
F	●	●	●	●	●	

STANDARD LAYOUT

01	UDR-10 ASSEMBLY	재질 <지정안함>		1	-
NO.	DESCRIPTION	MATERIAL	COLOR/FINISH	Q.TY	VENDOR
DRAW/DESIGNED	CHECKED	APPROVED	G.TOL	TITLE	
2016-10-27			±0.1	UDR-10 ASSEMBLY	
			UNIT	SCALE	MODEL
			mm	3:1	UADR-10S
SUNG MUN ELECTRONICS CO.,LTD			SIZE	DRAW NO.	UDR-10SA-01
			A4		1/1