

**HSF** RoHS **CAV** us **CE**

**SPECIFICATIONS**

Rated(额定参数): 300V,20A  
 Dielectric strength(抗电强度): AC2000V/1 Minute  
 Insulation Resistance(绝缘电阻):1000MΩ Min  
 Contact Resistance(接触电阻):20mΩ Max  
 Screw Torque(扭矩): 0.5Nm (4.4Lb.in)  
 Wire Range(线径):14~22AWG  
 Temp. range(操作温度): -40℃~+105℃  
 MAX Soldering(瞬时温度):+250℃,5s





Housing Material(塑件): PA66 (UL94 V-0)  
 Contact(端子): Brass, Tin plating(黄铜镀锡)  
 Screw (螺丝): M3.0, Steel, Ni plating(钢,镀锌)

PITCH RANGE IN MM	NOMINAL DIMENSION RANGE IN MM					
	OVER	OVER	OVER	OVER	OVER	OVER
TO 6	10	TO 10	30	TO 60	100	OVER 150
TO 10	24	TO 24	60	TO 100	150	OVER 150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70
						±1.00

**Ordering Information**

JL762B - 762 XX X X 1

Pitch 762=7.62PH  
 No.of pins 2P~22P  
 Housing Color  
 B=Black  
 G=Green  
 U=Blue  
 R=Red  
 W=White  
 Y=Yellow  
 O=Orange  
 E=Grey  
 Packing  
 O=Pe bog  
 T=Tube  
 A=Troy



Recommended P.C.B Layout

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	SCALE	FIT	TITLE:
A0	2018.10.07	NEW DRAWING	CHECK	X:XXX Angle	±0.10 ±3'	APPROVE	A4	1/1	PART NO. JL762B-762XXXX1
1				OPERATION			UNIT		TITLE: 7.62mm Terminal Blocks Female
				XX	±0.30		mm		
				X:XX	±0.20				
				X:XXX	±0.10				

**JILIN** 深圳市锦凌电子有限公司  
 SHENZHEN JINLING ELECTRONIC CO.,LTD  
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992