




REV.	DESCRIPTION	APPD	DATE


NOTES:

- MATERIAL:  
HOUSING: HIGH TEMPERATURE THERMOPLASTIC  
UL94V 0,COLOR:BLACK.  
CONTACT: COPPER ALLOYS.  
COVER: COPPER ALLOYS OR STEEL.
- PLATING:  
UNDERPLATE: NICKEL.  
CONTACT AREA: GOLD OVER NICKEL.  
SOLDER AREA: TIN OVER NICKEL.
- MULTIMEDIA CARD COMPATIBLE



RECOMMENDED P.C.B HOLE LAYOUT  
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

PIN NO.	NAME	TYPE	DESCRIPTION
1	DATA2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLK	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DATA0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(BIT1)



PART NO:	TF-011	MATERIAL:	
MODEL NO:		FINSH:	
UNIT:	MM	SIZE:	A4
TOLERANCES:	GENERAL	DR:	
X.X=±0.35	ANGLE:	CHK:	
X.XX=±0.25	X.XX=±3.0°	APP:	
X.XXX=±0.15	X.XX=±2.0°	SCALE:	1:1
		SHEET:	1 OF 2
		REV:	B/1

台湾汉博电子科技有限公司  
Taiwan Han Bo Electronic Technology Co.,Ltd.

TITLE: T-FLASH内焊 PUSH B Type

