

SPECIFICATIONS

Rated (额定参数): 300V, 8A
 Dielectric strength(抗电强度): AC1500V/1 Minute
 Insulation Resistance(绝缘电阻): 1000MΩ Min
 Contact Resistance(接触电阻): 20mΩ Max
 Screw Torque(扭矩): 0.2Nm (1.7Lb.in)
 Wire Range(线径): 16~28AWG
 Strip length(剥线长度): 6~7mm
 Temp. range(操作温度): -40°C~+105°C
 MAX Soldering(瞬时温度): +260°C, 5s

Housing Material(塑件): PA66 (UL94 V-0)
 Contact(端子): Phosphor Bronze, Tin plating(磷铜镀锡)
 Clamp(方块): Brass(黄铜), Ni plating(镀镍)
 Screw (螺丝): M2.0 Steel, Zinc plating(钢,镀锌)

PITCH RANGE		NOMINAL DIMENSION RANGE	
IN MM		IN MM	
OVER	10	OVER	30
TO	10	TO	60
6	24	TO	100
±0.10	±0.15	±0.25	±0.30
		±0.30	±0.50
		±0.50	±0.70
			±1.00

Ordering Information




JL15EDGKA-XXX XX G X 1

Pitch
 350=3.5PH 2P, 3P, 4P~24P
 381=3.81PH

No. of pins

Housing Color
 B=Black
 G=Green
 U=Blue
 R=Red
 W=White
 Y=Yellow
 O=Orange
 F=Grey

Packing
 O=Pe bog
 T=Tube
 A=Troy



OPERATION		DRAW		BEN		SCALE		FIT		PART NO.	
XX	±0.20	XX	UNIT	mm	mm	A4	1/1	JL15EDGKA-XXXXXXG1	3.50/3.81 Pitch Female Pluggable Terminal Blocks		
X.XX	±0.20	CHECK									
X.XXX	±0.10	APPROVE									
Angle	±3'										
DIM	TOL										
CHANGE											
MODIFICATION DESCRIPTION											
NEW DRAWING											
2017.01.05											
DATE											
REV											
1											

JIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992