

SPECIFICATIONS

Rated(额定参数): 125V,4A
 Dielectric strength(抗电强度): AC1250V/1 Minute
 Insulation Resistance(绝缘电阻):5000MΩ Min
 Contact Resistance(接触电阻):20mΩ Max
 Wire Range(线径):20~28AWG
 Strip length(剥线长度):8mm
 Temp. range(操作温度):-40C~+105C
 MAX Soldering(瞬时温度):+250C,5s




Housing Material(塑件): PA66 (UL94 V-0)
 Contact(端子): Phosphor Bronze, Tin plating(磷铜镀锡)

PITCH RANGE		NOMINAL DIMENSION RANGE					
IN MM		IN MM		IN MM		IN MM	
OVER	TO	OVER	TO	OVER	TO	OVER	TO
6	10	30	60	100	150	150	150
10	24	60	100	150	150	150	150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70	±1.00

Ordering Information

JL15EDGKD - 250 XX X X 1

Pitch 250=2.50PH
 No.of pins 2P,3P,4P~24P
 Housing Color
 B=Black
 G=Green
 U=Blue
 R=Red
 W=White
 Y=Yellow
 O=Orange
 E=Grey
 Packing
 O=Pe bag
 T=Tube
 A=Troy



OPERATION		DRAW		BEN		17.10.22		SCALE		FIT		PART NO.	
XX	±0.30							UNIT	mm				JL15EDGKD-250XXXX1
X:XX	±0.20	CHECK						SIZE	A4				2.50 Pitch Female
X:XXX	±0.10							SHEET	1/1				Pluggable Terminal Blocks
Angle	±3°	APPROVE						PROU.					
DIM	TOL	CHANGE											
1	2	3	4	5	6	7	8	9					
REV	DATE	MODIFICATION DESCRIPTION											
1	2017.10.22	NEW DRAWING											

JIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992