






SECTION A-A



电气性能/Electrical

参考标准/Standard: UL IEC  
额定电压/Rated voltage: 300V 320V  
额定电流/Rated current: 15A 20A  
接触电阻/Contact resistance: 20mΩ  
耐电压/Withstanding voltage: AC2000V/1Min  
绝缘电阻/Insulation resistance: 500MΩ/DC500V

机械性能/Mechanical

温度范围/Temp.Range: -40° C~+105° C  
瞬间温度/MAX Soldering: +250° C, for 5 Sec


尺寸/Dimensions

间距/Pitch: 5.00mm, 5.08mm  
极数/Poles: 2P-24P

材质及电镀/Material

塑件/Housing: PA66, UL94V-0  
焊针/Pin header: Brass, Tin plated

订购方式:  
HOW TO ORDER



TOLERANCES EXCEPT AS NOTED

|                | linear dimension |              |                |                 |      | fillet | chamfer |              |  short angle sid |  |  |  |  |  |                |                 |     |
|----------------|------------------|--------------|----------------|-----------------|------|--------|---------|--------------|-----------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|----------------|-----------------|-----|
| variable range | to 6             | over 6 to 30 | over 30 to 120 | over 120 to 480 |      | all    | to 6    | over 6 to 10 | to 10 to 50                                                                                         | over 50 to 120                                                                      | to 120                                                                              | all                                                                                 | to 5                                                                                | over 5 to 30                                                                        | over 30 to 120 | over 120 to 120 |     |
| tolerance      | ±0.1             | ±0.2         | ±0.3           | ±0.5            | ±0.9 | ±0.2   | ±0.5    | ±1           | 1°                                                                                                  | 30'                                                                                 | 20'                                                                                 | 10'                                                                                 | 0.5                                                                                 | 0.025                                                                               | 0.06           | 0.12            | 0.4 |

单位/UNITS mm 尺寸/SIZE A4 比例/SCALE

Cixi Dibo Electronics Co.,LTD

第一视角/FIRST ANGLE PROJECTION

名称/NAME DB2ER-5.08-XXP-F