



SIGN	DATE 10	DESCRIPTION
△	06 07	
△		
△		

**Material**

**Housing:** PA66 UL94V-0

**Solder Pin:** Brass With Tin plated

**Screw:** M3, steel, Zinc plated

**Electrical**

**Rated Voltage:** 300V

**Rated Current:** 30A

**Contact Resistance:** 20mΩ,

**Insulation Resistance:** 5000MΩ/1000V

**Withstanding Voltage:** 2000V/1Min

**Wire range:** 26-10AWG

**Mechanical**

**Temp. Range:** -40° C/+105° C

**Torque:** 0.5Nm

**Strip length:** 6-7mm

**MAX soldering:** +250° C5Sec

**RoHS Version**



Cixi Dibo Electronics Co.,LTD

PART NAME: TINAL BLOCK				TITLE:	
PART NO: DB910-7.62				DWG NAME: A1.DWG	
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO:	<b>Tolerance</b> L ±0.10 S ±0.20 R ±0.10 X ±0.05
陆少波				图例: 20 比例: 2/1 图例: A1	