




**P.C.B. LAYOUT**



Section: A-A



订购方式：  
HOW TO ORDER

### 电气性能/Electrical

参考标准/Standard: UL IEC  
 额定电压/Rated voltage: 300V 250V  
 额定电流/Rated current: 8A 15A  
 接触电阻/Contact resistance: 20mΩ  
 使用线径/Wire range: 26-16AWG 1.5mm<sup>2</sup>  
 耐电压/Withstanding voltage: AC2000V/1Min  
 绝缘电阻/Insulation resistance: 500MΩ/DC500V

### 机械性能/Mechanical


温度范围/Temp.Range: -40° C~+105° C  
 扭矩/Torque: 0.4Nm(3.541b`in)  
 剥线长度/Strip length: 6-7mm

### 尺寸/Dimensions

间距/Pitch: 5.0mm  
 极数/Poles: 2P-24P

### 材质及电镀/Material

塑件/Housing: PA66, UL94V-0  
 螺丝/Screws: M2.5, steel Zinc plated  
 方块/Cage: Brass, Ni plated  
 焊脚/Pin header: Brass, Snle plated



		linear dimension(Tolerances Standard GB/T 14486-2008)															
variable range	to	over 6	over 10	over 18	over 30	over 50	over 80	over 120	over 160	over 200	over 250	all	to 5	over 5	over 30	over 120	
		to 6	to 10	to 18	to 30	to 50	to 80	to 120	to 160	to 200	to 250			to 5	to 30	to 120	
tolerance		±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25	0.5	0.025	0.06	0.12	0.4

单位/UNITS	mm	尺寸/SIZE	A4	比例/SCALE	比例	第一视角/THIRD ANGLE PROJECTION	
Cixi Dibo Electronics Co.,LTD						名称/NAME	
						DB127V-5.0-XXP	