




SECTION A-A

宽脚针长3.5

订购方式：
HOW TO ORDER

电气性能/Electrical

参考标准/Standard: UL IEC

额定电压/Rated voltage: 300V 450V

额定电流/Rated current: 15A 24A

使用线径/Wire range: 22-14AWG 1.5mm²

耐电压/Withstanding voltage: AC2000V/1Min

绝缘电阻/Insulation resistance: 500MΩ/DC500V

机械性能/Mechanical

扭矩/Torque: 0.8

温度范围/Temp.Range: -40°C~+105°C

尺寸/Dimensions

间距/Pitch: 8.25mm

极数/Poles: 2p-26p

材质及电镀/Material

塑件/Housing: PA66, UL94V-0

螺丝/Screws: M3, steel, Ni Plated

焊脚/Pin header: Brass, Tin plated

	linear dimension(Tolerances Standard GB/T 14486-2008)											≡	—	□	//	⊥
variable range	to 6	over 6 to 10	over 10 to 18	over 18 to 30	over 30 to 50	over 50 to 80	over 80 to 120	over 120 to 160	over 160 to 200	over 200 to 250	over 250 to	all	to 5	over 5 to 30	over 30 to 120	over 120 to
tolerance	±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25	0.5	0.025	0.06	0.12	0.4

单位/UNITS	mm	尺寸/SIZE	A4	比例/SCALE	比例	第一视角/FIRST ANGLE PROJECTION	
Cixi Dibo Electronics Co.,LTD						名称/NAME	DBT30H-8.25-XXP