



## 3R Ceramic Surge Arresters

### SPECIFICATION

**Changzhou Wujin Jiangnan Discharge Tube Co.,Ltd**

---

Add:Zouqu Town Industrial Zone,Wujin Changzhou City,Jiangsu,China  
Tel: 0519-83631254                  Fax: 0519-83631533  
Email:[jiangnan@jiangnan-cn.cn](mailto:jiangnan@jiangnan-cn.cn)

---



## • Electrical Characteristics

TYPE: 3R230AL2			
DC spark-over voltage	230 $\pm 20$	V %	
Impulse spark-over voltage at 100V/ $\mu$ s - for 99% of measured values -typical values of distribution	<750 <700	V V	
at 1 kV/ $\mu$ s - for 99% of measured values - typical values of distribution	<800 <750	V V	
Service life 10 operations      50Hz, 1s 10 operations      8/20 $\mu$ s 300 operations      10/1000 $\mu$ s	10 10 100	A kA kA	
Insulation resistance at 100 Vdc	>10	G $\Omega$	
Capacitance at 1 MHz	<1	pF	
Arc voltage at 1 A Glow to arc transition current Glow voltage	~20 ~1 ~180	V A V	
Weight	~2.5	g	
Operation and storage temperature	-40...+90	°C	
Marking, blue	 3R230 3R -Three Electrode 230 -Nominal voltage		
P/N			



Dimensional drawing

