



3R Ceramic Surge Arresters

SPECIFICATION

Changzhou Wujin Jiangnan Discharge Tube Co.,Ltd

Add:Zouqu Town Industrial Zone,Wujin Changzhou City,Jiangsu,China

Tel: 0519-83631254 Fax: 0519-83631533

Email:jiangnan@jiangnan-cn.cn




·Electrical Characteristics

Type: 3R600AL4

DC spark-over voltage	600 ±20	V %
Impulse spark-over voltage at 100V/μs - for 99% of measured values -typical values of distribution at 1 kV/μs - for 99% of measured values - typical values of distribution	<1100 <1000 <1400 <1200	V V V V
Service life 10 operations 50Hz, 1s 10 operations [5x (+)&5x(-)] 8/20μs 1 operations 8/20μs 1 operations 10/350μs 300 operations [5x (+)&5x(-)] 10/1000μs	10 20 25 1 200	A kA kA KA A
Insulation resistance at 250 Vdc	>10	GΩ
Capacitance at 1 MHz	<1.5	pF
Arc voltage at 1 A Glow to arc transition current Glow voltage	~15 ~0.6 ~70	V A V
Weight	~2.0	g
Operation and storage temperature	-40...+125	°C
Marking, blue	<p> 3R600 3R -Two Electrode 600 -Nominal voltage</p>	



· Dimensional drawing



3R-AL4 Type ($\phi 8 \times 10$)