





SECTION A-A

电气性能/Electrical

参考标准/Standard: UL IEC
额定电压/Rated voltage: 300V 320V
额定电流/Rated current: 15A 20A
接触电阻/Contact resistance: 20mΩ
使用线径/Wire range: 28-14AWG 2.5mm²
耐电压/Withstanding voltage: AC2000V/1Min
绝缘电阻/Insulation resistance: 500MΩ/DC500V

机械性能/Mechanical


温度范围/Temp.Range: -40° C~+105° C
扭矩/Torque: 0.5Nm (4.5lb`in)
剥线长度/Strip length: 7-8mm

尺寸/Dimensions

间距/Pitch: 5.0mm, 5.08mm, 7.62mm
极数/Poles: 02P-24P

材质及电镀/Material

塑件/Housing: PA66, UL94V-0
螺丝/Screws: M3, steel Zinc plated
夹子/Clamp: Brass, Ni plated
方块/wire guard: Phosphor bronze, Ni plated

订购方式:
HOW TO ORDER

TOLERANCES EXCEPT AS NOTED

	linear dimension					fillet	chamfer	短角边/short angle sid	≡	—	□	∥	⊥
variable range	to 6	over 6 to 30	over 30 to 120	over 120 to 480	over 480 to	all	to 6	to 10	to 10	to 50	to 120	to 10	to 120
tolerance	±0.1	±0.2	±0.3	±0.5	±0.9	±0.2	±0.5	±1	1°	30'	20'	10'	0.5

单位/UNITS	mm	尺寸/SIZE	A4	比例/SCALE	第一视角/FIRST ANGLE PROJECTION
Cixi Dibo Electronics Co.,LTD					名称/NAME
					DB2EKB-5.0/5.08-XXP