








SPECIFICATIONS:

Current Rating: 3A AC,DC
Voltage Rating: 250V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 10mΩ Max.
Insulation Resistance: 1000MΩ Min.
Withstanding Voltage: 800V AC/minute
Pin Material: Brass/Tin over Nickel
Material: Nylon 6T, UL94V-0(Ivory)

Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	2.00	8.00	10P	18.00	24.00
3P	4.00	10.00	11P	20.00	26.00
4P	6.00	12.00	12P	22.00	28.00
5P	8.00	14.00	13P	24.00	30.00
6P	10.00	16.00	14P	26.00	32.00
7P	12.00	18.00	15P	28.00	34.00
8P	14.00	20.00	16P	30.00	36.00
9P	16.00	22.00			

CJTconn

CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	4:1	1 of 1
Draw BY:		Approved :
LIZQ		GONGYB

Title :		2.00mm PITCH	
		180° WAFER	
DRAW NO :		A2012WV-XP	REV A0

General Tolerance			ANGLE±
A0	NEW RELEASE	2013.04.17	
REV	DESCRIPTION	DATE	