



SCHEMATIC	
Model	DC-012B-2.5A
Center Pin	Ø2.0 mm
Center Pin	

	MATERIAL	PLATING
center pin	copper	nickel
terminal 1	brass	tin
terminal 2	copper alloy	tin
terminal 3	brass	tin
plastic	PBT	

REVISIONS					UNSPECIFIED TOLERANCES		DSND	DATE	SCALE: N/A	MODEL TYPE: DC POWER JACK			
ΔX					ANGLAR	±5°	DWN	DATE	VIEW:	PART NO.:			
ΔX					L ≤ 4	±0.2	CHKD	DATE	UNIT: mm	DWG NO.:			
ΔX					4 < L ≤ 16	±0.3	APPD	DATE	SIZE: A4	DC-012B-2.5A-2.0			
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4	XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION	
					L > 63	±0.5				1.0g	1/1	A0	