




GND			Vbus		D-	D+	Vbus			GND
A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2



主要特性:
 1 额定电流: 0.5A
 2 接触阻抗: 30mΩ MAX
 3 绝缘阻抗: 100MΩ MIN 250V DC
 4 耐压测试: 250V AC
 5 沾锡性: 温度250±5℃, 时间5±0.5s
 6 整体插入力: 3.57kgf MAX
 整体拔出力: 1.02kgf MIN

4	PLASTIC	HIGH TEMP	Black/White	UL 94V-0
3	Latch	STAINLESS STEEL	—	Ni Plated
2	TERMINAL	COPPER ALLOY	—	Gold Plated
1	SHELL	STAINLESS STEEL	—	Ni Plated
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

APPROVALS		DATE	ELECTRONICS CO.,LTD	
DRAWN	D.J.L/V	2017/12/26	Hirose	
CHECKED			USB CONNECTOR	
APPROVALS			PART NO.	TYPE-C-31-G-06
TOLERANCES ARE		±0.30	SCALE:	1:1
	10~30	±0.20	UNIT:	mm
	5~10	±0.15	DRAWING NO.	
	~5	±0.10	PROJ:	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	