



8-(1.4X0.5)



P C B Layout(copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

Model No.	PJ-3930-A	PJ-3930-B	PJ-3930-C

Schematic

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
DRAWN J.X.Zhang 2013/6/22 CHECKED APPROVALS TOLERANCES ARE 30%以上 ±0.30 ANGLE 10~30 ±0.20 5~10 ±0.15 ±2° ~5 ±0.10						
TITLE: PHONE JACKES PART NO. PJ-3930			ELECTRONICS CO.,LTD 			
DRAWN J.X.Zhang 2013/6/22 CHECKED APPROVALS		TITLE: PHONE JACKES PART NO. PJ-3930		SCALE: 1:1 SHEET 1 OF 1		
DRAWN J.X.Zhang 2013/6/22 CHECKED APPROVALS		TITLE: PHONE JACKES PART NO. PJ-3930		SCALE: 1:1 SHEET 1 OF 1		