






P.C.B Layout (copper-sided view)



Rating:0.5A 30V DC
Contact Resistance:100 mΩ Max.
Operating temperature:-20℃~70℃
Operating force:3~20N
Operating Life:5,000cycles

A=φ5	PJ-3133
Schematic	

				Contact Resistance:100 mΩ Max.			
				Operating temperature:-20℃~70℃			
				Operating force:3-20N			
				Operating Life:5,000cycles			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	
	A		NEW				