

REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD

Electrical

Material: Phosphor Bronze C5191





Plating: Tin-Plated

Wire Range: 26AWG~32AWG


Insulation Nom.Dia: ϕ .039"(1.0mm Max)

Applicable Housing: FHG12507 Series

Minimum Order Quantity :10,000 PCS






SECTION: A-A




SECTION: B-B

 THIRD ANGLE PROJECTION		GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 25/JUN/13	PART NO. FT12508-F2H	ITEM NO. FT12508	 Leader Of Industry		
		X.±.012(0.30)	X.'±5'	CHECKED BY JACOB	DATE 25/JUN/13	TITLE Wire to Board Pitch 1.25mm(Terminal)				
DESIGN UNITS Inch (metric)		X.XX±.008(0.20)	.X'±2"	DRAWN BY CHERRY	DATE 25/JUN/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			REV 0	SHEET NO. 1/2
SCALE 5:1	SIZE A4	X.XX±.006(0.15)	.XX'±1"							
		X.XXX±.004(0.10)	.XXX'±0.5'							

REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD



10,000Pcs/Reel



 THIRD ANGLE PROJECTION		GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 25/JUN/13	PART NO. FT12508-F2H	ITEM NO. FT12508	 Leader Of Industry		
		X.±.012(0.30)	X'.±5'	CHECKED BY JACOB	DATE 25/JUN/13	TITLE Wire to Board Pitch 1.25mm(Terminal)				
DESIGN UNITS Inch (metric)		X.X±.008(0.20)	X'.±2'	DRAWN BY CHERRY	DATE 25/JUN/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			REV 0	SHEET NO. 2/2
SCALE 5:1	SIZE A4	X.XX±.006(0.15)	XX'.±1'		X.XXX±.004(0.10)	XXX'.±0.5'				