





环保物料

TEL:0769-82001899



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $100\text{M}\Omega$ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer Nylon46, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
02	1.25	4.25
03	2.50	5.50
04	3.75	6.75
05	5.00	8.00
06	6.25	9.25
07	7.50	10.50
08	8.75	11.75
09	10.00	13.00
10	11.25	14.25
11	12.50	15.50
12	13.75	16.75
20	23.75	26.75

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1	
				X.	± 0.30	X°	$\pm 5^{\circ}$			CHKD	DATE	2010. 4. 12
				.X	± 0.20	.X°	$\pm 2^{\circ}$	APPD	PRODUCT NAME	1.25mm Crimp Style Connectors	UNITS	mm
				.XX	± 0.08	.XX°	$\pm 1^{\circ}$	VIEW	PART. NO.	M1250V-14-46	SCALE	1:1
				.XXX	± 0.03	.XXX°	$\pm 0.5^{\circ}$				DWG NO.	009
AO	MODIFICATION	DRAW	DATE									