



SPECIFICATION
 Contact Rating: 50mA, 12V DC
 Contact Resistance: 100mΩ max
 Insulation Resistance: 100mΩ min. 500V DC
 Dielectric Strength: 250V AC/1minute
 Travel: 0.13mm
 Operating Temp: -30°C ~ +85°C
 Storage Temp: -30°C ~ +80°C

PAPT NO	TS-1185EC-X-X-X
Operating Force	A:100gf B:160gf C:260gf
Height	H:A:1.8 B:1.85 C:1.92 D:2.0 E:2.5
Fixed column	A:With B:without

⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Lcp		—
②	Cover	—	1	Brass	Plating Nickel	—
①	Keystake	—	1	Lcp		—
ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK

					units: mm	DSND		DATE	SCALE: N/A	MODEL TYPE: TACT SWITCH			
					tolerance:	DWN		DATE	VIEW:	PART NO.:			
△X					X.X ±0.2mm	CHKD		DATE	UNIT: mm	DWG NO.:			
△X					X.XX ±0.1mm	APPD		DATE	SIZE: A4	TS-1185EC-X-X-X			
△X					X.XXX ±0.05mm					WEIGHT	SHEET	REVISION	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO., LIMITED				1.0g	1/1	A0	