








CIRCUIT DIAGRAM



SPECIFICATION

Contact Rating:	50mA,12V DC
Contact Resistance:	100mΩ max
Insulation Resistance:	100mΩ min.500V DC
Dielectric Strength:	250V AC/1minute
Travel:	0.25mm
Operating Temp:	-30℃~+85℃
Storage Temp:	-30℃~+80℃

P.C.B MOUNTING PATTERN DIMENSION



PAPT NO	TC-1103T-X-X
Operating force	B:160gf C:260gf
Height	H: 7.3
color	B:Black Y: Yellow

⑤	Terminal	—	4	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Pa46		—
②	Cover	—	1	Spcc	Plating Nickel	—
①	Keystake	—	1	Pa46		—
ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK

						DSND		DATE		SCALE: N/A	MODEL TYPE: TACT SWITCH				
					units: mm	DWN		DATE		VIEW: 	PART NO.:				
△X					tolerance:	CHKD		DATE		UNIT: mm	DWG NO.:				
△X					X.X ±0.2mm	APPD		DATE		SIZE: A4	TC-1103T-X-X				
△X					X.XX ±0.1mm										
MARK	DESCRIPTION		DATE	REVISED	APPROVED	X.XXX ±0.05mm									
REVISIONS						UNSPECIFIED TOLERANCES						XKB INDUSTRIAL PRECISION CO.,LIMITED			
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												WEIGHT	SHEET	REVISION	
												1.0g	1/1	A0	