


SPECIFICATION

Contact Rating : 50mA, 12V DC
 Contact Resistance : 100mΩ max
 Insulation Resistance : 100mΩ min. 500V DC
 Dielectric Strength : 250V AC/1minute
 Travel : 0.25mm
 Operating Temp : -20°C ~ +70°C
 Storage Temp : -30°C ~ +80°C

PAPT NO	TC-1101T-X-X-X
Operating Force	A: 100gf B: 160gf C: 260gf
Height	A: H: 4.3 B: H: 5.0
Yellow	B: Black W: White

SWITCH CONNECTOR

P.C.B MOUNTING HOLES



⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	LCP		—
②	Cover	—	1	Spcc	Plating Nickel	—
①	Keystake	—	1	Pa46		—
ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK

					units: mm	DSND		DATE		SCALE: N/A	MODEL TYPE: TACT SWITCH		
					tolerance:	DWN		DATE		VIEW:	PART NO.:		
					X.X ±0.2mm	CHKD		DATE		UNIT: mm	DWG NO.:		
					X.XX ±0.1mm	APPD		DATE		SIZE: A4	TC-1101T-X-X-X		
					X.XXX ±0.05mm	XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT	SHEET	REVISION
REVISIONS					UNSPECIFIED TOLERANCES						1.0g	1/1	A0
MARK	DESCRIPTION	DATE	REVISED	APPROVED									
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn													