



# SWITCH CONNECTOR

**NOTE:**  
 Rating: DC 12V 50mA  
 Operating Force: 200±100gf  
 Lifetime: 10,000 Cycles

PAPT NO	L
SS-3336S-02-L1	2.0
SS-3336S-02-L2	3.0
SS-3336S-02-L3	4.0

ITEM	PAPT NAME	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	8	Brass (0.30t)	ag Plated	
④	Contact spring	—	1	Phosphor branze	ag Plated	
③	Base	—	1	Pa46	Black	
②	Cover	—	1	Sus	Natural	
①	Keystake	—	1	Pa46	Black	

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°	DSND	DATE	SCALE: N/A	MODEL TYPE: SLIDE SWITCH		
△X					X.X	±0.2mm	DWN	DATE	VIEW:	PART NO.:		
△X					X.XX	±0.1mm	CHKD	DATE	UNIT: mm	DWG NO.:		
△X					X.XXX	±0.05mm	APPD	DATE	SIZE: A4	SS-3336S-02-X		
UNSPECIFIED TOLERANCES							XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g	SHEET 1/1	REVISION A0